

Life X

For all brew methods.



Life X Webpage

Keeping the promise.

All-purpose grinders, while marketed as versatile, often perform better in either espresso or filter brewing methods.

Grinders optimized for espresso can produce a muddy filter, while those designed for filter brewing may yield an under-extracted espresso with a lack of body. Life X offers the best of both worlds.



Clarity and body.

Life X is designed to handle a variety of brew settings, **all the way from Espresso to French Press**, thanks to the depth of its grinding chamber, combined with the variable impact burr geometry and advanced flap design, ensuring optimal particle size distribution for any brewing method.

X **Burrs**

Size matters.

The Life X features the innovative **XB50 burrs**, **manufactured by Ceado** without the use of screws. This design allows for the performance of larger 60 mm burrs, while minimizing retention and reducing coffee waste. The grinder also boasts the highest motor power-to-burr diameter ratio, ensuring exceptional durability and consistently precise performance, while minimizing the chance of jamming.



ceado. original burrs



ParallelModes.

Setting the dose has never been simpler with the Life X thanks to the **user-friendly interface** that makes it easy to switch between timed and manual dosing options, allowing you to customize your grind mode to your preferred brewing method. The grinder kits in the box, comprising of a **bean hopper and a dosing funnel**, grant perfect workflow for both manual dosing and programmed doses.

Designing Flavor.

life.X

Enhanced clarity
Low retention
Jam prevention
Manual and automatic modes
For all brew methods.



© Ceado srl - all rights reserved - 03/2025

XB50

ceado. original burrs

life.X

Ø 50 blind flat burrs multi-purpose

Technical data

Voltage - Power	220-240 V · 50-60 Hz / 300 W 110-120 V · 60 Hz / 3 A
Rpm 50 Hz / 60 Hz	1380 / 1650 rpm
Average Output (g/s)	1,6 (50 Hz) / 1,9 (60 Hz)
Net weight	5,4 kg
Gross weight	6,0 kg
Dimensions	150 x 200 x 355h mm
Burrs	XB50 Ø 50 blind flat burrs multi-purpose*
Hopper	Approximately 300 g
Funnel	Approximately 30 g
Dose setting	2 Programmable Times / Manual Dosing
Colors	● ● ● ●

*NSF version uses Steel burrs.

Designing Flavor.

